

KOLSTER-BRANDES LIMITED

FOOTSCRAY

SIDCUP

KENT

SERVICE DATA SUPPLEMENT

Issued
December, 1949

The following omissions and alterations, if added to existing Service Data Sheets, will bring them up to date:—

<p>Model No. DRP 20</p>	<p>All models produced from Serial Number 00325 will incorporate the following changes :-</p> <p>C14 (.005 mfd) connected between screened Lead and Pin 4 on V2.</p> <p>R18 (2.2 megohms) connected between Pin 4 of V2 and earth.</p>
<p>DRP 20/R</p>	<p>This Model is as CRP20/R except for the following :-</p> <p>R9 and C12 deleted.</p> <p>R5 and R8 changed to 1.5 megohms.</p> <p>R10 changed to 2.2 megohms.</p> <p>R11 (47000 ohms) added between R10 and L16.</p> <p>C11 to be connected to Junction of R11 and L16.</p> <p>Screened Lead on Tag 8A on Switch to be connected to the Junction of R10 and R11.</p>
<p>EG 30</p>	<p>Amend Frequency of Supply to Read 50 to 60 cycles.</p>
<p>EGT 10</p>	<p>Frequency Supply 50 cycles only (Synchronous.)</p>